

CROWN CLAMP [TM4]

Datasheet, 04.12.2020, V1

Engineered and made in Switzerland


Standard clamp:

- Ø2.20mm to Ø7.50mm
- Depth 0.80mm, 1.40mm (2.00mm only for Ø7.00)
- Optional (on request)
 - o Plastic insert in the clip, avoids marks



Large format clamp:

- Ø7.50mm to Ø13.00mm
- Depth and diameter tailored to your crown
- Optional (on request)
 - Plastic insert in the clip, avoids marks





Extra large clamp:

- Ø13.00mm to Ø18.00mm
- Depth and diameter tailored to your crown
- Optional (on request)
 - Plastic insert in the clip, avoids marks



Clamp with crown support:

- 3 available formats
 - o Standard Ø2.20mm to Ø7.50mm
 - o Large format Ø7.50mm to Ø13.00mm
 - Very large format Ø13.00mm to Ø18.00mm
- Depth 0.80mm, 1.40mm (2.00mm only for Ø7.00)
- Plastic crown support (fixed, depending on crown)





Crown Clamp with various shapes:

- Customised to your crown
- Vacuum



Clamp with crown support and spring stop:

- Tailored to your crown
- 3 available formats
 - o Standard Ø2.20mm to Ø7.50mm
 - o Large format Ø7.50mm to Ø13.00mm
 - o Very large format Ø13.00mm to Ø18.00mm





Roxer SA