

Aérox 5 & 10

Drying cabinet

Datasheet, 23.03.2023, V2.0

 Engineered and made in Switzerland

The Aérox 5 and 10 are machines used to dry watches after the condensation test. The temperature is adjustable from 25 to 55 °C by means of an electronic controller and is uniform throughout the cabinet.

Machine functions

- Dry watches after the condensation test
- Removable trays for loading
- Temperature adjustable by electronic regulator
- Uniform temperature in the cabinet
- Large drying capacity (ideal for large series)



Aérox 5

Technical specifications

	Aérox 5	Aérox 10
Supply voltage:	230 V / 50 Hz	230 V / 50 Hz
Power :	1400 W	1400 W
Capacity :	Up to 100 watches (5 trays)	Up to 200 watches (10 trays)
Heating temperature :	25 to 55 °C	25 to 55 °C
Weight :	34 kg	50 kg
Dimensions closed device (l/d/h) :	330 x 435 x 610 mm	330 x 435 x 940 mm
Dimensions open device (l/d/h) :	330 x 715 x 660 mm	330 x 715 x 990 mm