


PDA

Staking-tool to remove hands


Datasheet, 01.06.2023, V1.1

 Engineered and made in Switzerland

This Staking-tool allows to remove hands without support on the dial.

The components and their functions

- Pusher
 - Applies the counter-axis on the hand axis
- Knurling-roller
 - Adjust the working height and remove the hand
- Clamp lever
 - Blocks the counter-axis
- Teflon table
 - Sliding area where comes the movement-holder




Technical specifications

Weight : 1,2 kg
Dimensions (l/d/h) : 110 x 120 x 140 mm

Tooling needed

Interchangeable parts composed of a counter-axis and a fork made according to your needs.

- Counter shaft
 - Shaft holding the hand axis during the remove
- Fork
 - Housing under the hand



Universal movement-holder

Allows a universal tightening of the movement.

The universal movement holder can be purchased separately and used for several applications.

